

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580489

Luminaire Tested: **HC435D010-HM43040930-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC435D010-HM43040930-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2612.9 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580489

CATALOG NUMBER: HC435D010-HM43040930-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580489

CATALOG NUMBER: HC435D010-HM43040930-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	260592
5°	260832
10°	261331
15°	265150
20°	258533
25°	242565
30°	214552
35°	163150
40°	102793
45°	59012
50°	31298
55°	13010
60°	3454
65°	2948
70°	2200
75°	1906
80°	1421
85°	2830



TEST NUMBER: P580489

CATALOG NUMBER: HC435D010-HM43040930-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.3	7.7
10°-20°	581.4	22.3
20°-30°	811.4	31.1
30°-40°	667.7	25.6
40°-50°	275.0	10.5
50°-60°	62.0	2.4
60°-70°	10.0	0.4
70°-80°	3.7	0.1
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.2	61.0
0°-40°	2260.9	86.5
0°-60°	2597.9	99.4
0°-90°	2612.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2612.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2113	
5°	2107	200
15°	2076	581
25°	1782	811
35°	1084	668
45°	338	275
55°	60	62
65°	10	10
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P580489

CATALOG NUMBER: HC435D010-HM43040930-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2112.7
2.5°	2102.6
5°	2106.6
7.5°	2098.5
10°	2086.5
12.5°	2080.4
15°	2076.4
17.5°	2040.2
20°	1969.6
22.5°	1881.0
25°	1782.3
27.5°	1663.5
30°	1506.4
32.5°	1313.1
35°	1083.5
37.5°	851.9
40°	638.4
42.5°	465.2
45°	338.3
47.5°	241.7
50°	163.1
52.5°	102.7
55°	60.5
57.5°	30.2
60°	14.0
62.5°	12.1
65°	10.1
67.5°	8.1
70°	6.1
72.5°	4.0
75°	4.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)