

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580187

Luminaire Tested: **HC425D010-HM40525927-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525927-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2017.1 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580187

CATALOG NUMBER: HC425D010-HM40525927-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P580187

CATALOG NUMBER: HC425D010-HM40525927-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169588
5°	170867
10°	172993
15°	177345
20°	178647
25°	173537
30°	159105
35°	130912
40°	95434
45°	61943
50°	34924
55°	16580
60°	6537
65°	4057
70°	2741
75°	1811
80°	852
85°	1698



TEST NUMBER: P580187

CATALOG NUMBER: HC425D010-HM40525927-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	6.5
10°-20°	391.5	19.4
20°-30°	580.7	28.8
30°-40°	536.4	26.6
40°-50°	280.1	13.9
50°-60°	76.8	3.8
60°-70°	14.8	0.7
70°-80°	4.2	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1104.1	54.7
0°-40°	1640.4	81.3
0°-60°	1997.3	99.0
0°-90°	2017.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2017.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1375	
5°	1380	132
15°	1389	392
25°	1275	581
35°	869	536
45°	355	280
55°	77	77
65°	14	15
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P580187

CATALOG NUMBER: HC425D010-HM40525927-41WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1374.9
2.5°	1371.2
5°	1380.0
7.5°	1383.8
10°	1381.2
12.5°	1383.8
15°	1388.8
17.5°	1383.8
20°	1361.0
22.5°	1324.4
25°	1275.1
27.5°	1208.1
30°	1117.1
32.5°	1002.1
35°	869.4
37.5°	730.5
40°	592.7
42.5°	466.3
45°	355.1
47.5°	260.3
50°	182.0
52.5°	121.4
55°	77.1
57.5°	45.5
60°	26.5
62.5°	19.0
65°	13.9
67.5°	10.2
70°	7.6
72.5°	5.1
75°	3.8
77.5°	2.5
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)