

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580526

Luminaire Tested: **HC435D010-HM43040940-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC435D010-HM43040940-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3389.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580526

CATALOG NUMBER: HC435D010-HM43040940-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580526

CATALOG NUMBER: HC435D010-HM43040940-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59			59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54			54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49			49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278218
5°	279554
10°	281458
15°	284279
20°	279535
25°	266682
30°	242297
35°	195449
40°	135608
45°	89033
50°	59640
55°	42450
60°	36264
65°	41707
70°	44683
75°	43034
80°	38783
85°	35664



TEST NUMBER: P580526

CATALOG NUMBER: HC435D010-HM43040940-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.2	6.3
10°-20°	625.4	18.5
20°-30°	893.5	26.4
30°-40°	798.2	23.6
40°-50°	409.4	12.1
50°-60°	186.1	5.5
60°-70°	138.8	4.1
70°-80°	94.4	2.8
80°-90°	28.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1734.1	51.2
0°-40°	2532.3	74.7
0°-60°	3127.8	92.3
0°-90°	3389.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3389.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2256	
5°	2258	215
15°	2226	625
25°	1960	894
35°	1298	798
45°	510	409
55°	197	186
65°	143	139
75°	90	94
85°	25	28
90°	0	



TEST NUMBER: P580526

CATALOG NUMBER: HC435D010-HM43040940-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2255.6
2.5°	2247.2
5°	2257.8
7.5°	2257.8
10°	2247.2
12.5°	2236.8
15°	2226.2
17.5°	2194.7
20°	2129.6
22.5°	2049.8
25°	1959.5
27.5°	1846.1
30°	1701.2
32.5°	1516.4
35°	1298.0
37.5°	1064.8
40°	842.2
42.5°	657.4
45°	510.4
47.5°	399.0
50°	310.8
52.5°	243.7
55°	197.4
57.5°	165.9
60°	147.0
62.5°	142.9
65°	142.9
67.5°	138.6
70°	123.9
72.5°	107.1
75°	90.3
77.5°	71.4
80°	54.6
82.5°	39.9
85°	25.2
87.5°	10.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)