

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580210

Luminaire Tested: **HC425D010-HM40525930-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC425D010-HM40525930-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2029.2 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580210

CATALOG NUMBER: HC425D010-HM40525930-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580210

CATALOG NUMBER: HC425D010-HM40525930-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	172030
5°	171115
10°	167996
15°	164461
20°	157409
25°	146386
30°	129552
35°	102257
40°	76515
45°	58873
50°	47743
55°	39590
60°	35030
65°	32426
70°	29933
75°	27498
80°	24932
85°	19955



TEST NUMBER: P580210

CATALOG NUMBER: HC425D010-HM40525930-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	6.4
10°-20°	361.2	17.8
20°-30°	490.4	24.2
30°-40°	424.8	20.9
40°-50°	266.7	13.1
50°-60°	167.8	8.3
60°-70°	110.2	5.4
70°-80°	60.8	3.0
80°-90°	16.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	982.2	48.4
0°-40°	1407.0	69.3
0°-60°	1841.5	90.8
0°-90°	2029.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2029.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1395	
5°	1382	131
15°	1288	361
25°	1076	490
35°	679	425
45°	338	267
55°	184	168
65°	111	110
75°	58	61
85°	14	17
90°	0	



TEST NUMBER: P580210

CATALOG NUMBER: HC425D010-HM40525930-41MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1394.7
2.5°	1386.3
5°	1382.0
7.5°	1368.0
10°	1341.3
12.5°	1314.6
15°	1287.9
17.5°	1251.3
20°	1199.2
22.5°	1140.2
25°	1075.6
27.5°	1001.1
30°	909.6
32.5°	798.5
35°	679.1
37.5°	569.5
40°	475.2
42.5°	400.7
45°	337.5
47.5°	289.6
50°	248.8
52.5°	213.7
55°	184.1
57.5°	158.9
60°	142.0
62.5°	126.6
65°	111.1
67.5°	95.6
70°	83.0
72.5°	68.9
75°	57.7
77.5°	44.9
80°	35.1
82.5°	23.9
85°	14.1
87.5°	5.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)