

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580532

Luminaire Tested: **HC435D010-HM43040940-41NDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580532  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC435D010-HM43040940-41NDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3107.6 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580532

CATALOG NUMBER: HC435D010-HM43040940-41NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P580532

CATALOG NUMBER: HC435D010-HM43040940-41NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	457723
5°	457132
10°	448227
15°	416790
20°	358449
25°	287940
30°	224807
35°	157398
40°	80766
45°	40993
50°	20532
55°	7656
60°	3108
65°	2452
70°	1515
75°	1001
80°	1492
85°	0



TEST NUMBER: P580532

CATALOG NUMBER: HC435D010-HM43040940-41NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	349.1	11.2
10°-20°	900.9	29.0
20°-30°	970.6	31.2
30°-40°	637.7	20.5
40°-50°	198.3	6.4
50°-60°	38.9	1.3
60°-70°	8.3	0.3
70°-80°	3.0	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2220.6	71.5
0°-40°	2858.3	92.0
0°-60°	3095.5	99.6
0°-90°	3107.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3107.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3711	
5°	3692	349
15°	3264	901
25°	2116	971
35°	1045	638
45°	235	198
55°	36	39
65°	8	8
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P580532

CATALOG NUMBER: HC435D010-HM43040940-41NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3710.9
2.5°	3692.0
5°	3692.0
7.5°	3662.7
10°	3578.7
12.5°	3444.4
15°	3263.9
17.5°	3022.4
20°	2730.8
22.5°	2415.9
25°	2115.7
27.5°	1836.6
30°	1578.4
32.5°	1335.0
35°	1045.3
37.5°	728.4
40°	501.6
42.5°	346.3
45°	235.0
47.5°	159.5
50°	107.0
52.5°	67.2
55°	35.6
57.5°	14.7
60°	12.6
62.5°	10.5
65°	8.4
67.5°	6.3
70°	4.2
72.5°	4.2
75°	2.1
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)