

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580223

Luminaire Tested: **HC425D010-HM40525935-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580223  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC425D010-HM40525935-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2363.8 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580223

CATALOG NUMBER: HC425D010-HM40525935-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P580223

CATALOG NUMBER: HC425D010-HM40525935-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	198747
5°	200249
10°	202752
15°	207852
20°	209375
25°	203370
30°	186466
35°	153423
40°	111842
45°	72583
50°	40931
55°	19419
60°	7647
65°	4757
70°	3210
75°	2097
80°	1065
85°	2123



TEST NUMBER: P580223

CATALOG NUMBER: HC425D010-HM40525935-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.4	6.5
10°-20°	458.9	19.4
20°-30°	680.6	28.8
30°-40°	628.6	26.6
40°-50°	328.2	13.9
50°-60°	89.9	3.8
60°-70°	17.3	0.7
70°-80°	4.8	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1293.9	54.7
0°-40°	1922.5	81.3
0°-60°	2340.6	99.0
0°-90°	2363.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2363.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1611	
5°	1617	154
15°	1628	459
25°	1494	681
35°	1019	629
45°	416	328
55°	90	90
65°	16	17
75°	4	5
85°	2	1
90°	0	



TEST NUMBER: P580223

CATALOG NUMBER: HC425D010-HM40525935-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1611.3
2.5°	1606.9
5°	1617.3
7.5°	1621.7
10°	1618.8
12.5°	1621.7
15°	1627.7
17.5°	1621.7
20°	1595.1
22.5°	1552.0
25°	1494.3
27.5°	1415.9
30°	1309.2
32.5°	1174.4
35°	1018.9
37.5°	856.0
40°	694.6
42.5°	546.4
45°	416.1
47.5°	305.1
50°	213.3
52.5°	142.1
55°	90.3
57.5°	53.3
60°	31.0
62.5°	22.2
65°	16.3
67.5°	11.9
70°	8.9
72.5°	5.9
75°	4.4
77.5°	2.9
80°	1.5
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)