

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580572

Luminaire Tested: **HC440D010-HM43040830-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580572  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC440D010-HM43040830-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3843.7 lumens  
Efficiency: N/A  
Efficacy: 93.7 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580572

CATALOG NUMBER: HC440D010-HM43040830-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580572

CATALOG NUMBER: HC440D010-HM43040830-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	333860
5°	331767
10°	324707
15°	317518
20°	302834
25°	280332
30°	243835
35°	184141
40°	133466
45°	104278
50°	89172
55°	77137
60°	71072
65°	65056
70°	60768
75°	55663
80°	52137
85°	49958



TEST NUMBER: P580572

CATALOG NUMBER: HC440D010-HM43040830-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	253.1	6.6
10°-20°	696.5	18.1
20°-30°	936.6	24.4
30°-40°	770.1	20.0
40°-50°	472.9	12.3
50°-60°	327.3	8.5
60°-70°	223.2	5.8
70°-80°	124.3	3.2
80°-90°	39.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1886.1	49.1
0°-40°	2656.3	69.1
0°-60°	3456.6	89.9
0°-90°	3843.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3843.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2707	
5°	2680	253
15°	2486	697
25°	2060	937
35°	1223	770
45°	598	473
55°	359	327
65°	223	223
75°	117	124
85°	35	40
90°	0	



TEST NUMBER: P580572

CATALOG NUMBER: HC440D010-HM43040830-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2706.7
2.5°	2687.6
5°	2679.5
7.5°	2649.6
10°	2592.5
12.5°	2540.9
15°	2486.5
17.5°	2407.7
20°	2307.1
22.5°	2187.6
25°	2059.8
27.5°	1905.0
30°	1712.0
32.5°	1475.6
35°	1222.9
37.5°	1005.5
40°	828.9
42.5°	693.0
45°	597.8
47.5°	524.5
50°	464.7
52.5°	410.4
55°	358.7
57.5°	320.7
60°	288.1
62.5°	255.5
65°	222.9
67.5°	195.6
70°	168.5
72.5°	141.4
75°	116.8
77.5°	92.4
80°	73.4
82.5°	54.4
85°	35.3
87.5°	19.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)