

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592719

Luminaire Tested: **HC425D010-HM40525950-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592719  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC425D010-HM40525950-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2214.8 lumens  
Efficiency: N/A  
Efficacy: 82.6 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592719

CATALOG NUMBER: HC425D010-HM40525950-41MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P592719

CATALOG NUMBER: HC425D010-HM40525950-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52																			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47																			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44																			
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	187769
5°	186778
10°	183364
15°	179503
20°	171822
25°	159764
30°	141402
35°	111608
40°	83519
45°	64245
50°	52118
55°	43246
60°	38237
65°	35403
70°	32638
75°	29976
80°	27276
85°	21795



TEST NUMBER: P592719

CATALOG NUMBER: HC425D010-HM40525950-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.6	6.4
10°-20°	394.2	17.8
20°-30°	535.2	24.2
30°-40°	463.7	20.9
40°-50°	291.1	13.1
50°-60°	183.2	8.3
60°-70°	120.3	5.4
70°-80°	66.4	3.0
80°-90°	18.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.1	48.4
0°-40°	1535.7	69.3
0°-60°	2010.0	90.8
0°-90°	2214.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2214.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1522	
5°	1508	143
15°	1406	394
25°	1174	535
35°	741	464
45°	368	291
55°	201	183
65°	121	120
75°	63	66
85°	15	18
90°	0	



TEST NUMBER: P592719

CATALOG NUMBER: HC425D010-HM40525950-41MDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1522.3
2.5°	1513.1
5°	1508.5
7.5°	1493.1
10°	1464.0
12.5°	1434.8
15°	1405.7
17.5°	1365.8
20°	1309.0
22.5°	1244.5
25°	1173.9
27.5°	1092.6
30°	992.8
32.5°	871.6
35°	741.2
37.5°	621.5
40°	518.7
42.5°	437.4
45°	368.3
47.5°	316.1
50°	271.6
52.5°	233.3
55°	201.1
57.5°	173.4
60°	155.0
62.5°	138.1
65°	121.3
67.5°	104.3
70°	90.5
72.5°	75.2
75°	62.9
77.5°	49.1
80°	38.4
82.5°	26.1
85°	15.4
87.5°	6.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)