

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580258

Luminaire Tested: **HC430D010-HM43040827-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040827-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2896.4 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580258

CATALOG NUMBER: HC430D010-HM43040827-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P580258

CATALOG NUMBER: HC430D010-HM43040827-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243521
5°	245355
10°	248418
15°	254653
20°	256538
25°	249193
30°	228468
35°	187996
40°	137041
45°	88945
50°	50160
55°	23806
60°	9399
65°	5837
70°	3931
75°	2573
80°	1279
85°	2547



TEST NUMBER: P580258

CATALOG NUMBER: HC430D010-HM43040827-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.2	6.5
10°-20°	562.2	19.4
20°-30°	833.9	28.8
30°-40°	770.2	26.6
40°-50°	402.2	13.9
50°-60°	110.2	3.8
60°-70°	21.2	0.7
70°-80°	5.9	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1585.4	54.7
0°-40°	2355.6	81.3
0°-60°	2868.0	99.0
0°-90°	2896.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2896.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1974	
5°	1982	189
15°	1994	562
25°	1831	834
35°	1248	770
45°	510	402
55°	111	110
65°	20	21
75°	5	6
85°	2	1
90°	0	



TEST NUMBER: P580258

CATALOG NUMBER: HC430D010-HM43040827-41WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1974.3
2.5°	1968.8
5°	1981.6
7.5°	1987.0
10°	1983.4
12.5°	1987.0
15°	1994.2
17.5°	1987.0
20°	1954.4
22.5°	1901.7
25°	1831.0
27.5°	1734.8
30°	1604.1
32.5°	1439.0
35°	1248.5
37.5°	1048.8
40°	851.1
42.5°	669.6
45°	509.9
47.5°	373.8
50°	261.4
52.5°	174.2
55°	110.7
57.5°	65.3
60°	38.1
62.5°	27.2
65°	20.0
67.5°	14.6
70°	10.9
72.5°	7.2
75°	5.4
77.5°	3.6
80°	1.8
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)