

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580260

Luminaire Tested: **HC4R30D010-HM43040827-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P580260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R30D010-HM43040827-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2812.9 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580260

CATALOG NUMBER: HC4R30D010-HM43040827-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P580260

CATALOG NUMBER: HC4R30D010-HM43040827-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318774
5°	325601
10°	338446
15°	338588
20°	313033
25°	270506
30°	220064
35°	161660
40°	93454
45°	43662
50°	20187
55°	7011
60°	2220
65°	1576
70°	1298
75°	858
80°	0
85°	0



TEST NUMBER: P580260

CATALOG NUMBER: HC4R30D010-HM43040827-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.7	9.0
10°-20°	734.8	26.1
20°-30°	904.9	32.2
30°-40°	660.7	23.5
40°-50°	215.3	7.7
50°-60°	36.0	1.3
60°-70°	5.5	0.2
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1893.5	67.3
0°-40°	2554.1	90.8
0°-60°	2805.4	99.7
0°-90°	2812.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2812.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2584	
5°	2630	254
15°	2652	735
25°	1988	905
35°	1074	661
45°	250	215
55°	33	36
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P580260

CATALOG NUMBER: HC4R30D010-HM43040827-42RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2584.4
2.5°	2586.2
5°	2629.7
7.5°	2680.5
10°	2702.2
12.5°	2695.0
15°	2651.5
17.5°	2542.6
20°	2384.8
22.5°	2194.4
25°	1987.6
27.5°	1771.9
30°	1545.1
32.5°	1313.0
35°	1073.6
37.5°	832.5
40°	580.4
42.5°	379.0
45°	250.3
47.5°	165.0
50°	105.2
52.5°	61.7
55°	32.6
57.5°	12.7
60°	9.0
62.5°	7.2
65°	5.4
67.5°	3.6
70°	3.6
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)