

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580273

Luminaire Tested: **HC430D010-HM43040830-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040830-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2544.8 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580273

CATALOG NUMBER: HC430D010-HM43040830-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580273

CATALOG NUMBER: HC430D010-HM43040830-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72																			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49																			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253796
5°	254035
10°	254517
15°	258241
20°	251812
25°	236251
30°	208969
35°	158889
40°	100120
45°	57477
50°	30492
55°	12666
60°	3404
65°	2860
70°	2128
75°	1859
80°	1350
85°	2689



TEST NUMBER: P580273

CATALOG NUMBER: HC430D010-HM43040830-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.1	7.7
10°-20°	566.3	22.3
20°-30°	790.3	31.1
30°-40°	650.3	25.6
40°-50°	267.9	10.5
50°-60°	60.4	2.4
60°-70°	9.7	0.4
70°-80°	3.6	0.1
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1551.7	61.0
0°-40°	2202.0	86.5
0°-60°	2530.2	99.4
0°-90°	2544.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2544.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2058	
5°	2052	195
15°	2022	566
25°	1736	790
35°	1055	650
45°	330	268
55°	59	60
65°	10	10
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P580273

CATALOG NUMBER: HC430D010-HM43040830-41WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2057.6
2.5°	2047.8
5°	2051.7
7.5°	2043.8
10°	2032.1
12.5°	2026.2
15°	2022.3
17.5°	1987.0
20°	1918.4
22.5°	1832.0
25°	1735.9
27.5°	1620.1
30°	1467.2
32.5°	1278.9
35°	1055.2
37.5°	829.8
40°	621.8
42.5°	453.1
45°	329.5
47.5°	235.4
50°	158.9
52.5°	100.1
55°	58.9
57.5°	29.4
60°	13.8
62.5°	11.7
65°	9.8
67.5°	7.9
70°	5.9
72.5°	3.9
75°	3.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)