

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580276

Luminaire Tested: **HC430D010-HM43040830-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040830-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2723.3 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580276

CATALOG NUMBER: HC430D010-HM43040830-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580276

CATALOG NUMBER: HC430D010-HM43040830-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63			63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54			54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51			51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	353237
5°	346811
10°	328952
15°	307583
20°	279351
25°	247193
30°	205608
35°	148258
40°	92536
45°	53378
50°	30108
55°	14344
60°	8239
65°	6275
70°	4219
75°	2812
80°	2770
85°	2689



TEST NUMBER: P580276

CATALOG NUMBER: HC430D010-HM43040830-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.8	9.6
10°-20°	671.9	24.7
20°-30°	826.4	30.3
30°-40°	613.7	22.5
40°-50°	249.5	9.2
50°-60°	69.1	2.5
60°-70°	21.5	0.8
70°-80°	7.2	0.3
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1760.2	64.6
0°-40°	2373.9	87.2
0°-60°	2692.5	98.9
0°-90°	2723.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2723.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2864	
5°	2801	262
15°	2409	672
25°	1816	826
35°	985	614
45°	306	250
55°	67	69
65°	22	21
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P580276

CATALOG NUMBER: HC430D010-HM43040830-41NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2863.8
2.5°	2836.4
5°	2801.0
7.5°	2730.4
10°	2626.4
12.5°	2518.6
15°	2408.7
17.5°	2277.3
20°	2128.2
22.5°	1977.2
25°	1816.3
27.5°	1641.8
30°	1443.6
32.5°	1218.1
35°	984.6
37.5°	765.0
40°	574.7
42.5°	419.7
45°	306.0
47.5°	219.7
50°	156.9
52.5°	107.8
55°	66.7
57.5°	43.2
60°	33.4
62.5°	27.4
65°	21.5
67.5°	15.7
70°	11.7
72.5°	9.8
75°	5.9
77.5°	3.9
80°	3.9
82.5°	1.9
85°	1.9
87.5°	1.9
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)