

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580641

Luminaire Tested: **HC440D010-HM43040930-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040930-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3954.4 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580641

CATALOG NUMBER: HC440D010-HM43040930-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P580641

CATALOG NUMBER: HC440D010-HM43040930-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55	55	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319441
5°	324128
10°	334301
15°	357193
20°	378493
25°	374348
30°	335986
35°	261507
40°	177166
45°	110593
50°	47858
55°	16021
60°	4046
65°	2714
70°	1695
75°	1144
80°	1705
85°	0



TEST NUMBER: P580641

CATALOG NUMBER: HC440D010-HM43040930-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.5	6.4
10°-20°	794.1	20.1
20°-30°	1244.2	31.5
30°-40°	1073.8	27.2
40°-50°	493.8	12.5
50°-60°	83.8	2.1
60°-70°	9.5	0.2
70°-80°	3.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2289.7	57.9
0°-40°	3363.5	85.1
0°-60°	3941.1	99.7
0°-90°	3954.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3954.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2590	
5°	2618	251
15°	2797	794
25°	2751	1244
35°	1737	1074
45°	634	494
55°	74	84
65°	9	9
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P580641

CATALOG NUMBER: HC440D010-HM43040930-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2589.8
2.5°	2589.8
5°	2617.8
7.5°	2643.4
10°	2669.1
12.5°	2722.7
15°	2797.2
17.5°	2860.2
20°	2883.5
22.5°	2848.6
25°	2750.6
27.5°	2592.1
30°	2359.0
32.5°	2065.3
35°	1736.7
37.5°	1405.6
40°	1100.3
42.5°	841.5
45°	634.0
47.5°	445.3
50°	249.4
52.5°	137.5
55°	74.5
57.5°	37.3
60°	16.4
62.5°	11.7
65°	9.3
67.5°	7.0
70°	4.7
72.5°	4.7
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)