

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580284

Luminaire Tested: **HC430D010-HM43040830-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580284  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC430D010-HM43040830-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2774.5 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580284

CATALOG NUMBER: HC430D010-HM43040830-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580284

CATALOG NUMBER: HC430D010-HM43040830-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	240993
5°	239486
10°	234390
15°	229203
20°	218603
25°	202362
30°	176012
35°	132930
40°	96336
45°	75287
50°	64380
55°	55676
60°	51287
65°	46960
70°	43854
75°	40223
80°	37647
85°	36088



TEST NUMBER: P580284

CATALOG NUMBER: HC430D010-HM43040830-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.7	6.6
10°-20°	502.8	18.1
20°-30°	676.1	24.4
30°-40°	555.9	20.0
40°-50°	341.4	12.3
50°-60°	236.3	8.5
60°-70°	161.1	5.8
70°-80°	89.8	3.2
80°-90°	28.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1361.5	49.1
0°-40°	1917.4	69.1
0°-60°	2495.1	89.9
0°-90°	2774.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2774.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1954	
5°	1934	183
15°	1795	503
25°	1487	676
35°	883	556
45°	432	341
55°	259	236
65°	161	161
75°	84	90
85°	26	29
90°	0	



TEST NUMBER: P580284

CATALOG NUMBER: HC430D010-HM43040830-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1953.8
2.5°	1940.0
5°	1934.2
7.5°	1912.5
10°	1871.4
12.5°	1834.1
15°	1794.9
17.5°	1738.0
20°	1665.4
22.5°	1579.1
25°	1486.9
27.5°	1375.0
30°	1235.8
32.5°	1065.2
35°	882.8
37.5°	725.8
40°	598.3
42.5°	500.2
45°	431.6
47.5°	378.6
50°	335.5
52.5°	296.2
55°	258.9
57.5°	231.5
60°	207.9
62.5°	184.4
65°	160.9
67.5°	141.2
70°	121.6
72.5°	102.0
75°	84.4
77.5°	66.7
80°	53.0
82.5°	39.3
85°	25.5
87.5°	13.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)