

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580651

Luminaire Tested: **HC440D010-HM43040935-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040935-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3152.3 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580651

CATALOG NUMBER: HC440D010-HM43040935-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580651

CATALOG NUMBER: HC440D010-HM43040935-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93																
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85																
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72																
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49																
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314371
5°	314668
10°	315263
15°	319880
20°	311904
25°	292635
30°	258847
35°	196835
40°	124015
45°	71205
50°	37764
55°	15677
60°	4194
65°	3532
70°	2633
75°	2288
80°	1776
85°	3538



TEST NUMBER: P580651

CATALOG NUMBER: HC440D010-HM43040935-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.7	7.7
10°-20°	701.4	22.3
20°-30°	978.9	31.1
30°-40°	805.5	25.6
40°-50°	331.8	10.5
50°-60°	74.7	2.4
60°-70°	12.0	0.4
70°-80°	4.5	0.1
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1922.0	61.0
0°-40°	2727.5	86.5
0°-60°	3134.1	99.4
0°-90°	3152.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3152.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2549	
5°	2541	242
15°	2505	701
25°	2150	979
35°	1307	806
45°	408	332
55°	73	75
65°	12	12
75°	5	4
85°	2	2
90°	0	



TEST NUMBER: P580651

CATALOG NUMBER: HC440D010-HM43040935-41WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2548.7
2.5°	2536.6
5°	2541.4
7.5°	2531.7
10°	2517.1
12.5°	2509.8
15°	2505.0
17.5°	2461.3
20°	2376.2
22.5°	2269.2
25°	2150.2
27.5°	2006.9
30°	1817.4
32.5°	1584.1
35°	1307.2
37.5°	1027.7
40°	770.2
42.5°	561.3
45°	408.2
47.5°	291.6
50°	196.8
52.5°	123.9
55°	72.9
57.5°	36.4
60°	17.0
62.5°	14.6
65°	12.1
67.5°	9.8
70°	7.3
72.5°	4.8
75°	4.8
77.5°	2.5
80°	2.5
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)