

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580295

Luminaire Tested: **HC430D010-HM43040835-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580295  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC430D010-HM43040835-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3142.4 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580295

CATALOG NUMBER: HC430D010-HM43040835-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P580295

CATALOG NUMBER: HC430D010-HM43040835-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	264219
5°	266194
10°	269522
15°	276298
20°	278327
25°	270356
30°	247880
35°	203957
40°	148682
45°	96499
50°	54401
55°	25827
60°	10213
65°	6333
70°	4256
75°	2812
80°	1350
85°	2689



TEST NUMBER: P580295

CATALOG NUMBER: HC430D010-HM43040835-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	205.3	6.5
10°-20°	610.0	19.4
20°-30°	904.8	28.8
30°-40°	835.7	26.6
40°-50°	436.3	13.9
50°-60°	119.6	3.8
60°-70°	23.1	0.7
70°-80°	6.5	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.0	54.7
0°-40°	2555.7	81.3
0°-60°	3111.6	99.0
0°-90°	3142.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3142.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2142	
5°	2150	205
15°	2164	610
25°	1986	905
35°	1354	836
45°	553	436
55°	120	120
65°	22	23
75°	6	6
85°	2	1
90°	0	



TEST NUMBER: P580295

CATALOG NUMBER: HC430D010-HM43040835-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2142.1
2.5°	2136.1
5°	2149.9
7.5°	2155.8
10°	2151.9
12.5°	2155.8
15°	2163.7
17.5°	2155.8
20°	2120.4
22.5°	2063.3
25°	1986.5
27.5°	1882.2
30°	1740.4
32.5°	1561.3
35°	1354.5
37.5°	1137.9
40°	923.4
42.5°	726.4
45°	553.2
47.5°	405.5
50°	283.5
52.5°	189.1
55°	120.1
57.5°	70.8
60°	41.4
62.5°	29.6
65°	21.7
67.5°	15.8
70°	11.8
72.5°	7.9
75°	5.9
77.5°	3.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)