

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580723

Luminaire Tested: **HC445D010-HM44560835-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560835-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3860.4 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580723

CATALOG NUMBER: HC445D010-HM44560835-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580723

CATALOG NUMBER: HC445D010-HM44560835-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	384999
5°	385355
10°	386091
15°	391735
20°	381971
25°	358370
30°	316986
35°	241044
40°	151887
45°	87201
50°	46246
55°	19204
60°	5156
65°	4349
70°	3246
75°	2812
80°	2131
85°	4246



TEST NUMBER: P580723

CATALOG NUMBER: HC445D010-HM44560835-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.0	7.7
10°-20°	859.0	22.3
20°-30°	1198.8	31.1
30°-40°	986.5	25.6
40°-50°	406.4	10.5
50°-60°	91.6	2.4
60°-70°	14.7	0.4
70°-80°	5.5	0.1
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2353.8	61.0
0°-40°	3340.3	86.5
0°-60°	3838.2	99.4
0°-90°	3860.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3860.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3121	
5°	3112	296
15°	3068	859
25°	2633	1199
35°	1601	986
45°	500	406
55°	89	92
65°	15	15
75°	6	5
85°	3	2
90°	0	



TEST NUMBER: P580723

CATALOG NUMBER: HC445D010-HM44560835-41WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3121.3
2.5°	3106.4
5°	3112.3
7.5°	3100.4
10°	3082.6
12.5°	3073.6
15°	3067.7
17.5°	3014.1
20°	2910.0
22.5°	2779.1
25°	2633.2
27.5°	2457.7
30°	2225.6
32.5°	1939.9
35°	1600.8
37.5°	1258.7
40°	943.3
42.5°	687.3
45°	499.9
47.5°	357.0
50°	241.0
52.5°	151.7
55°	89.3
57.5°	44.7
60°	20.9
62.5°	17.8
65°	14.9
67.5°	11.9
70°	9.0
72.5°	5.9
75°	5.9
77.5°	3.0
80°	3.0
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)