

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580348

Luminaire Tested: **HC430D010-HM43040930-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040930-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2334.7 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580348

CATALOG NUMBER: HC430D010-HM43040930-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580348

CATALOG NUMBER: HC430D010-HM43040930-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63			63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54			54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51			51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302814
5°	297309
10°	281997
15°	263668
20°	239474
25°	211903
30°	176254
35°	127102
40°	79333
45°	45755
50°	25829
55°	12301
60°	7031
65°	5399
70°	3606
75°	2431
80°	2415
85°	2406



TEST NUMBER: P580348

CATALOG NUMBER: HC430D010-HM43040930-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.4	9.6
10°-20°	576.0	24.7
20°-30°	708.4	30.3
30°-40°	526.1	22.5
40°-50°	213.9	9.2
50°-60°	59.2	2.5
60°-70°	18.4	0.8
70°-80°	6.2	0.3
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1508.9	64.6
0°-40°	2035.0	87.2
0°-60°	2308.2	98.9
0°-90°	2334.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2334.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2455	
5°	2401	224
15°	2065	576
25°	1557	708
35°	844	526
45°	262	214
55°	57	59
65°	18	18
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P580348

CATALOG NUMBER: HC430D010-HM43040930-41NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2455.0
2.5°	2431.4
5°	2401.2
7.5°	2340.6
10°	2251.5
12.5°	2159.0
15°	2064.8
17.5°	1952.1
20°	1824.4
22.5°	1694.9
25°	1557.0
27.5°	1407.4
30°	1237.5
32.5°	1044.2
35°	844.1
37.5°	655.8
40°	492.7
42.5°	359.8
45°	262.3
47.5°	188.4
50°	134.6
52.5°	92.5
55°	57.2
57.5°	37.0
60°	28.5
62.5°	23.6
65°	18.5
67.5°	13.4
70°	10.0
72.5°	8.5
75°	5.1
77.5°	3.4
80°	3.4
82.5°	1.7
85°	1.7
87.5°	1.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)