

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580759

Luminaire Tested: **HC445D010-HM44560927-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560927-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2997.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580759

CATALOG NUMBER: HC445D010-HM44560927-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580759

CATALOG NUMBER: HC445D010-HM44560927-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298879
5°	299154
10°	299719
15°	304097
20°	296520
25°	278223
30°	246086
35°	187122
40°	117896
45°	67699
50°	35903
55°	14903
60°	3996
65°	3386
70°	2524
75°	2192
80°	1705
85°	3397



TEST NUMBER: P580759

CATALOG NUMBER: HC445D010-HM44560927-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.8	7.7
10°-20°	666.8	22.3
20°-30°	930.6	31.1
30°-40°	765.8	25.6
40°-50°	315.5	10.5
50°-60°	71.1	2.4
60°-70°	11.4	0.4
70°-80°	4.3	0.1
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1827.3	61.0
0°-40°	2593.1	86.5
0°-60°	2979.6	99.4
0°-90°	2997.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2997.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2423	
5°	2416	230
15°	2381	667
25°	2044	931
35°	1243	766
45°	388	315
55°	69	71
65°	12	11
75°	5	4
85°	2	2
90°	0	



TEST NUMBER: P580759

CATALOG NUMBER: HC445D010-HM44560927-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2423.1
2.5°	2411.5
5°	2416.1
7.5°	2406.9
10°	2393.0
12.5°	2386.2
15°	2381.4
17.5°	2339.9
20°	2259.0
22.5°	2157.4
25°	2044.3
27.5°	1908.0
30°	1727.8
32.5°	1506.1
35°	1242.7
37.5°	977.0
40°	732.2
42.5°	533.6
45°	388.1
47.5°	277.1
50°	187.1
52.5°	117.8
55°	69.3
57.5°	34.7
60°	16.2
62.5°	13.9
65°	11.6
67.5°	9.2
70°	7.0
72.5°	4.6
75°	4.6
77.5°	2.4
80°	2.4
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)