

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580777

Luminaire Tested: **HC445D010-HM44560930-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560930-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3255.3 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580777

CATALOG NUMBER: HC445D010-HM44560930-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580777

CATALOG NUMBER: HC445D010-HM44560930-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	324646
5°	324957
10°	325571
15°	330339
20°	322103
25°	302217
30°	267307
35°	203264
40°	128072
45°	73525
50°	38992
55°	16193
60°	4342
65°	3677
70°	2705
75°	2383
80°	1776
85°	3538



TEST NUMBER: P580777

CATALOG NUMBER: HC445D010-HM44560930-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.6	7.7
10°-20°	724.3	22.3
20°-30°	1010.9	31.1
30°-40°	831.9	25.6
40°-50°	342.7	10.5
50°-60°	77.2	2.4
60°-70°	12.4	0.4
70°-80°	4.6	0.1
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1984.9	61.0
0°-40°	2816.7	86.5
0°-60°	3236.6	99.4
0°-90°	3255.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3255.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2632	
5°	2624	250
15°	2587	724
25°	2221	1011
35°	1350	832
45°	422	343
55°	75	77
65°	13	12
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P580777

CATALOG NUMBER: HC445D010-HM44560930-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2632.0
2.5°	2619.5
5°	2624.5
7.5°	2614.5
10°	2599.4
12.5°	2591.9
15°	2586.9
17.5°	2541.7
20°	2453.9
22.5°	2343.5
25°	2220.6
27.5°	2072.6
30°	1876.8
32.5°	1635.9
35°	1349.9
37.5°	1061.3
40°	795.4
42.5°	579.6
45°	421.5
47.5°	301.1
50°	203.2
52.5°	127.9
55°	75.3
57.5°	37.6
60°	17.6
62.5°	15.0
65°	12.6
67.5°	10.0
70°	7.5
72.5°	5.0
75°	5.0
77.5°	2.5
80°	2.5
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)