

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580369

Luminaire Tested: **HC430D010-HM43040935-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040935-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2708.7 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580369

CATALOG NUMBER: HC430D010-HM43040935-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P580369

CATALOG NUMBER: HC430D010-HM43040935-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74		
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69		
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60		
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56		
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52		
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313742
5°	319509
10°	329366
15°	325716
20°	299093
25°	258026
30°	210265
35°	155682
40°	89332
45°	43173
50°	20532
55°	7183
60°	2590
65°	1547
70°	1262
75°	858
80°	0
85°	0



TEST NUMBER: P580369

CATALOG NUMBER: HC430D010-HM43040935-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.2	9.2
10°-20°	707.1	26.1
20°-30°	863.5	31.9
30°-40°	634.8	23.4
40°-50°	210.4	7.8
50°-60°	37.2	1.4
60°-70°	5.6	0.2
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1818.9	67.1
0°-40°	2453.7	90.6
0°-60°	2701.3	99.7
0°-90°	2708.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2708.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2544	
5°	2580	248
15°	2551	707
25°	1896	864
35°	1034	635
45°	248	210
55°	33	37
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P580369

CATALOG NUMBER: HC430D010-HM43040935-41MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2543.6
2.5°	2545.4
5°	2580.5
7.5°	2619.2
10°	2629.7
12.5°	2605.1
15°	2550.7
17.5°	2438.4
20°	2278.6
22.5°	2092.6
25°	1895.9
27.5°	1690.5
30°	1476.3
32.5°	1262.2
35°	1033.9
37.5°	802.2
40°	554.8
42.5°	366.9
45°	247.5
47.5°	165.0
50°	107.0
52.5°	63.2
55°	33.4
57.5°	14.1
60°	10.5
62.5°	7.0
65°	5.3
67.5°	3.5
70°	3.5
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)