

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580802

Luminaire Tested: **HC445D010-HM44560935-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560935-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3866.6 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580802

CATALOG NUMBER: HC445D010-HM44560935-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P580802

CATALOG NUMBER: HC445D010-HM44560935-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	569499
5°	568777
10°	557694
15°	518577
20°	445975
25°	358261
30°	279699
35°	195826
40°	100506
45°	51023
50°	25560
55°	9548
60°	3873
65°	3035
70°	1911
75°	1239
80°	1847
85°	0



TEST NUMBER: P580802

CATALOG NUMBER: HC445D010-HM44560935-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.3	11.2
10°-20°	1121.0	29.0
20°-30°	1207.6	31.2
30°-40°	793.4	20.5
40°-50°	246.7	6.4
50°-60°	48.5	1.3
60°-70°	10.3	0.3
70°-80°	3.8	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2762.9	71.5
0°-40°	3556.3	92.0
0°-60°	3851.4	99.6
0°-90°	3866.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3866.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4617	
5°	4594	434
15°	4061	1121
25°	2632	1208
35°	1300	793
45°	292	247
55°	44	48
65°	10	10
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P580802

CATALOG NUMBER: HC445D010-HM44560935-41NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	4617.1
2.5°	4593.7
5°	4593.7
7.5°	4557.1
10°	4452.7
12.5°	4285.5
15°	4061.0
17.5°	3760.6
20°	3397.6
22.5°	3005.8
25°	2632.4
27.5°	2285.1
30°	1963.8
32.5°	1660.9
35°	1300.5
37.5°	906.2
40°	624.2
42.5°	430.8
45°	292.5
47.5°	198.5
50°	133.2
52.5°	83.6
55°	44.4
57.5°	18.3
60°	15.7
62.5°	13.0
65°	10.4
67.5°	7.9
70°	5.3
72.5°	5.3
75°	2.6
77.5°	2.6
80°	2.6
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)