

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580370

Luminaire Tested: **HC430D010-HM43040935-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040935-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2596.5 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580370

CATALOG NUMBER: HC430D010-HM43040935-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P580370

CATALOG NUMBER: HC430D010-HM43040935-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	382433
5°	381938
10°	374493
15°	348216
20°	299474
25°	240578
30°	187819
35°	131499
40°	67498
45°	34259
50°	17174
55°	6408
60°	2590
65°	2043
70°	1262
75°	858
80°	1279
85°	0



TEST NUMBER: P580370

CATALOG NUMBER: HC430D010-HM43040935-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.6	11.2
10°-20°	752.7	29.0
20°-30°	810.9	31.2
30°-40°	532.8	20.5
40°-50°	165.7	6.4
50°-60°	32.5	1.3
60°-70°	6.9	0.3
70°-80°	2.6	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1855.3	71.5
0°-40°	2388.1	92.0
0°-60°	2586.3	99.6
0°-90°	2596.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2596.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3100	
5°	3085	292
15°	2727	753
25°	1768	811
35°	873	533
45°	196	166
55°	30	33
65°	7	7
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P580370

CATALOG NUMBER: HC430D010-HM43040935-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3100.5
2.5°	3084.7
5°	3084.7
7.5°	3060.2
10°	2990.0
12.5°	2877.8
15°	2726.9
17.5°	2525.3
20°	2281.5
22.5°	2018.4
25°	1767.7
27.5°	1534.4
30°	1318.7
32.5°	1115.4
35°	873.3
37.5°	608.6
40°	419.2
42.5°	289.3
45°	196.4
47.5°	133.3
50°	89.5
52.5°	56.1
55°	29.8
57.5°	12.3
60°	10.5
62.5°	8.8
65°	7.0
67.5°	5.3
70°	3.5
72.5°	3.5
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)