

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580372

Luminaire Tested: **HC430D010-HM43040935-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC430D010-HM43040935-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2533.3 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580372

CATALOG NUMBER: HC430D010-HM43040935-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580372

CATALOG NUMBER: HC430D010-HM43040935-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89	89	89	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79	79	79	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70	70	70	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63	63	63	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57	57	57	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52	52	52	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47	47	47	47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44	44	44	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40	40	40	40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37	37	37	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214769
5°	213633
10°	209729
15°	205324
20°	196525
25°	182751
30°	161755
35°	127659
40°	95531
45°	73490
50°	59621
55°	49439
60°	43738
65°	40452
70°	37362
75°	34313
80°	31183
85°	24908



TEST NUMBER: P580372

CATALOG NUMBER: HC430D010-HM43040935-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.1	6.4
10°-20°	450.9	17.8
20°-30°	612.2	24.2
30°-40°	530.4	20.9
40°-50°	333.0	13.1
50°-60°	209.4	8.3
60°-70°	137.6	5.4
70°-80°	75.9	3.0
80°-90°	20.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1226.2	48.4
0°-40°	1756.6	69.3
0°-60°	2299.0	90.8
0°-90°	2533.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2533.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1741	
5°	1725	163
15°	1608	451
25°	1343	612
35°	848	530
45°	421	333
55°	230	209
65°	139	138
75°	72	76
85°	18	21
90°	0	



TEST NUMBER: P580372

CATALOG NUMBER: HC430D010-HM43040935-41MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1741.2
2.5°	1730.7
5°	1725.4
7.5°	1707.9
10°	1674.5
12.5°	1641.1
15°	1607.9
17.5°	1562.2
20°	1497.2
22.5°	1423.5
25°	1342.8
27.5°	1249.7
30°	1135.7
32.5°	997.0
35°	847.8
37.5°	710.9
40°	593.3
42.5°	500.3
45°	421.3
47.5°	361.6
50°	310.7
52.5°	266.8
55°	229.9
57.5°	198.3
60°	177.3
62.5°	157.9
65°	138.6
67.5°	119.3
70°	103.6
72.5°	86.0
75°	72.0
77.5°	56.2
80°	43.9
82.5°	29.9
85°	17.6
87.5°	7.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)