

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592751

Luminaire Tested: **HC4R30D010-HM43040950-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P592751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R30D010-HM43040950-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2719.1 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592751

CATALOG NUMBER: HC4R30D010-HM43040950-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P592751

CATALOG NUMBER: HC4R30D010-HM43040950-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74		
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69		
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60		
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56		
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52		
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	308130
5°	314730
10°	327161
15°	327274
20°	302598
25°	261483
30°	212729
35°	156269
40°	90330
45°	42214
50°	19496
55°	6795
60°	2171
65°	1547
70°	1262
75°	858
80°	0
85°	0



TEST NUMBER: P592751

CATALOG NUMBER: HC4R30D010-HM43040950-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.2	9.0
10°-20°	710.3	26.1
20°-30°	874.8	32.2
30°-40°	638.6	23.5
40°-50°	208.1	7.7
50°-60°	34.8	1.3
60°-70°	5.4	0.2
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1830.3	67.3
0°-40°	2468.9	90.8
0°-60°	2711.8	99.7
0°-90°	2719.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2719.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2498	
5°	2542	245
15°	2563	710
25°	1921	875
35°	1038	639
45°	242	208
55°	32	35
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P592751

CATALOG NUMBER: HC4R30D010-HM43040950-42RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2498.1
2.5°	2499.9
5°	2541.9
7.5°	2591.0
10°	2612.1
12.5°	2605.0
15°	2562.9
17.5°	2457.8
20°	2305.3
22.5°	2121.2
25°	1921.3
27.5°	1712.8
30°	1493.6
32.5°	1269.2
35°	1037.8
37.5°	804.6
40°	561.0
42.5°	366.4
45°	242.0
47.5°	159.5
50°	101.6
52.5°	59.6
55°	31.6
57.5°	12.3
60°	8.8
62.5°	7.0
65°	5.3
67.5°	3.5
70°	3.5
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)