

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580872

Luminaire Tested: **HC4R50D010-HM44560835-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P580872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R50D010-HM44560835-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4876.9 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580872

CATALOG NUMBER: HC4R50D010-HM44560835-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P580872

CATALOG NUMBER: HC4R50D010-HM44560835-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	552662
5°	564518
10°	586789
15°	587009
20°	542741
25°	469017
30°	381548
35°	280284
40°	162015
45°	75688
50°	34982
55°	12172
60°	3873
65°	2743
70°	2272
75°	1477
80°	0
85°	0



TEST NUMBER: P580872

CATALOG NUMBER: HC4R50D010-HM44560835-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.8	9.0
10°-20°	1274.0	26.1
20°-30°	1569.0	32.2
30°-40°	1145.4	23.5
40°-50°	373.3	7.7
50°-60°	62.4	1.3
60°-70°	9.7	0.2
70°-80°	3.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3282.8	67.3
0°-40°	4428.2	90.8
0°-60°	4863.9	99.7
0°-90°	4876.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4876.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4481	
5°	4559	440
15°	4597	1274
25°	3446	1569
35°	1861	1145
45°	434	373
55°	57	62
65°	9	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P580872

CATALOG NUMBER: HC4R50D010-HM44560835-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4480.6
2.5°	4483.8
5°	4559.3
7.5°	4647.3
10°	4685.0
12.5°	4672.4
15°	4596.9
17.5°	4408.3
20°	4134.8
22.5°	3804.6
25°	3446.2
27.5°	3072.0
30°	2678.9
32.5°	2276.4
35°	1861.4
37.5°	1443.2
40°	1006.2
42.5°	657.1
45°	433.9
47.5°	286.2
50°	182.3
52.5°	106.9
55°	56.6
57.5°	22.0
60°	15.7
62.5°	12.6
65°	9.4
67.5°	6.3
70°	6.3
72.5°	3.1
75°	3.1
77.5°	3.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)