

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580876

Luminaire Tested: **HC450D010-HM44560835-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580876  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC450D010-HM44560835-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4540.5 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580876

CATALOG NUMBER: HC450D010-HM44560835-41MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580876

CATALOG NUMBER: HC450D010-HM44560835-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	384949
5°	382903
10°	375908
15°	367984
20°	352254
25°	327544
30°	289896
35°	228817
40°	171225
45°	131717
50°	106845
55°	88621
60°	78374
65°	72527
70°	66935
75°	61478
80°	55831
85°	44438



TEST NUMBER: P580876

CATALOG NUMBER: HC450D010-HM44560835-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	292.4	6.4
10°-20°	808.1	17.8
20°-30°	1097.3	24.2
30°-40°	950.6	20.9
40°-50°	596.8	13.1
50°-60°	375.4	8.3
60°-70°	246.6	5.4
70°-80°	136.0	3.0
80°-90°	37.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2197.8	48.4
0°-40°	3148.4	69.3
0°-60°	4120.6	90.8
0°-90°	4540.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4540.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3121	
5°	3092	292
15°	2882	808
25°	2407	1097
35°	1520	951
45°	755	597
55°	412	375
65°	248	247
75°	129	136
85°	31	37
90°	0	



TEST NUMBER: P580876

CATALOG NUMBER: HC450D010-HM44560835-41MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3120.9
2.5°	3101.9
5°	3092.5
7.5°	3061.1
10°	3001.3
12.5°	2941.5
15°	2881.7
17.5°	2799.9
20°	2683.6
22.5°	2551.4
25°	2406.7
27.5°	2240.0
30°	2035.4
32.5°	1786.9
35°	1519.6
37.5°	1274.2
40°	1063.4
42.5°	896.6
45°	755.1
47.5°	648.0
50°	556.8
52.5°	478.2
55°	412.1
57.5°	355.5
60°	317.7
62.5°	283.2
65°	248.5
67.5°	214.0
70°	185.6
72.5°	154.2
75°	129.0
77.5°	100.6
80°	78.6
82.5°	53.5
85°	31.4
87.5°	12.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)