

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580913

Luminaire Tested: **HC450D010-HM44560927-41NDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580913  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC450D010-HM44560927-41NDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3358.8 lumens  
Efficiency: N/A  
Efficacy: 70.0 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580913

CATALOG NUMBER: HC450D010-HM44560927-41NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580913

CATALOG NUMBER: HC450D010-HM44560927-41NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	295092
5°	292889
10°	285278
15°	277753
20°	265332
25°	247193
30°	217657
35°	171673
40°	124610
45°	91545
50°	74473
55°	62471
60°	56616
65°	52010
70°	48434
75°	44226
80°	39849
85°	34673



TEST NUMBER: P580913

CATALOG NUMBER: HC450D010-HM44560927-41NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.0	6.6
10°-20°	610.1	18.2
20°-30°	827.0	24.6
30°-40°	709.7	21.1
40°-50°	419.0	12.5
50°-60°	265.5	7.9
60°-70°	178.4	5.3
70°-80°	98.5	2.9
80°-90°	27.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.2	49.4
0°-40°	2369.8	70.6
0°-60°	3054.4	90.9
0°-90°	3358.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3358.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2392	
5°	2366	223
15°	2175	610
25°	1816	827
35°	1140	710
45°	525	419
55°	290	266
65°	178	178
75°	93	98
85°	24	28
90°	0	



TEST NUMBER: P580913

CATALOG NUMBER: HC450D010-HM44560927-41NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2392.4
2.5°	2375.3
5°	2365.5
7.5°	2333.8
10°	2277.7
12.5°	2228.8
15°	2175.1
17.5°	2106.7
20°	2021.4
22.5°	1926.2
25°	1816.3
27.5°	1686.8
30°	1528.2
32.5°	1340.2
35°	1140.1
37.5°	947.1
40°	773.9
42.5°	629.9
45°	524.8
47.5°	449.2
50°	388.1
52.5°	336.9
55°	290.5
57.5°	253.8
60°	229.5
62.5°	205.0
65°	178.2
67.5°	156.2
70°	134.3
72.5°	112.2
75°	92.8
77.5°	73.3
80°	56.1
82.5°	39.1
85°	24.5
87.5°	9.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)