

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580421

Luminaire Tested: **HC435D010-HM43040830-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC435D010-HM43040830-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3753.1 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580421

CATALOG NUMBER: HC435D010-HM43040830-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P580421

CATALOG NUMBER: HC435D010-HM43040830-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315543
5°	317924
10°	321888
15°	329994
20°	332407
25°	322890
30°	296049
35°	243604
40°	177569
45°	115251
50°	64955
55°	30838
60°	12162
65°	7559
70°	5121
75°	3384
80°	1705
85°	3397



TEST NUMBER: P580421

CATALOG NUMBER: HC435D010-HM43040830-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.2	6.5
10°-20°	728.5	19.4
20°-30°	1080.6	28.8
30°-40°	998.0	26.6
40°-50°	521.1	13.9
50°-60°	142.8	3.8
60°-70°	27.5	0.7
70°-80°	7.8	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2054.3	54.7
0°-40°	3052.3	81.3
0°-60°	3716.2	99.0
0°-90°	3753.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3753.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2558	
5°	2568	245
15°	2584	729
25°	2372	1081
35°	1618	998
45°	661	521
55°	143	143
65°	26	28
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P580421

CATALOG NUMBER: HC435D010-HM43040830-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2558.2
2.5°	2551.3
5°	2567.7
7.5°	2574.7
10°	2570.0
12.5°	2574.7
15°	2584.2
17.5°	2574.7
20°	2532.4
22.5°	2464.3
25°	2372.5
27.5°	2247.9
30°	2078.6
32.5°	1864.6
35°	1617.8
37.5°	1359.0
40°	1102.8
42.5°	867.6
45°	660.7
47.5°	484.3
50°	338.5
52.5°	225.7
55°	143.4
57.5°	84.6
60°	49.3
62.5°	35.3
65°	25.9
67.5°	18.8
70°	14.2
72.5°	9.4
75°	7.1
77.5°	4.7
80°	2.4
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)