

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580427

Luminaire Tested: **HC435D010-HM43040830-41NDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580427  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC435D010-HM43040830-41NDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3233.8 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580427

CATALOG NUMBER: HC435D010-HM43040830-41NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580427

CATALOG NUMBER: HC435D010-HM43040830-41NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	284102
5°	281980
10°	274645
15°	267410
20°	255448
25°	237979
30°	209553
35°	165274
40°	119957
45°	88160
50°	71710
55°	60149
60°	54519
65°	50054
70°	46631
75°	42605
80°	38428
85°	33258



TEST NUMBER: P580427

CATALOG NUMBER: HC435D010-HM43040830-41NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	214.7	6.6
10°-20°	587.4	18.2
20°-30°	796.2	24.6
30°-40°	683.2	21.1
40°-50°	403.4	12.5
50°-60°	255.7	7.9
60°-70°	171.7	5.3
70°-80°	94.8	2.9
80°-90°	26.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1598.3	49.4
0°-40°	2281.6	70.6
0°-60°	2940.7	90.9
0°-90°	3233.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3233.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2303	
5°	2277	215
15°	2094	587
25°	1749	796
35°	1098	683
45°	505	403
55°	280	256
65°	172	172
75°	89	95
85°	24	27
90°	0	



TEST NUMBER: P580427

CATALOG NUMBER: HC435D010-HM43040830-41NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2303.3
2.5°	2286.8
5°	2277.4
7.5°	2246.9
10°	2192.8
12.5°	2145.8
15°	2094.1
17.5°	2028.3
20°	1946.1
22.5°	1854.4
25°	1748.6
27.5°	1624.1
30°	1471.3
32.5°	1290.4
35°	1097.6
37.5°	911.9
40°	745.0
42.5°	606.4
45°	505.4
47.5°	432.4
50°	373.7
52.5°	324.4
55°	279.7
57.5°	244.5
60°	221.0
62.5°	197.4
65°	171.5
67.5°	150.4
70°	129.3
72.5°	108.1
75°	89.4
77.5°	70.5
80°	54.1
82.5°	37.7
85°	23.5
87.5°	9.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)