

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592764

Luminaire Tested: **HC435D010-HM43040850-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC435D010-HM43040850-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3198.4 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592764

CATALOG NUMBER: HC435D010-HM43040850-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P592764

CATALOG NUMBER: HC435D010-HM43040850-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318959
5°	319274
10°	319859
15°	324554
20°	316459
25°	296922
30°	262622
35°	199695
40°	125818
45°	72252
50°	38302
55°	15913
60°	4268
65°	3619
70°	2669
75°	2335
80°	1776
85°	3538



TEST NUMBER: P592764

CATALOG NUMBER: HC435D010-HM43040850-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.2	7.7
10°-20°	711.7	22.3
20°-30°	993.2	31.1
30°-40°	817.3	25.6
40°-50°	336.7	10.5
50°-60°	75.9	2.4
60°-70°	12.2	0.4
70°-80°	4.5	0.1
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1950.1	61.0
0°-40°	2767.4	86.5
0°-60°	3179.9	99.4
0°-90°	3198.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3198.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2586	
5°	2579	245
15°	2542	712
25°	2182	993
35°	1326	817
45°	414	337
55°	74	76
65°	12	12
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P592764

CATALOG NUMBER: HC435D010-HM43040850-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2585.9
2.5°	2573.6
5°	2578.6
7.5°	2568.7
10°	2553.8
12.5°	2546.5
15°	2541.6
17.5°	2497.2
20°	2410.9
22.5°	2302.4
25°	2181.7
27.5°	2036.2
30°	1843.9
32.5°	1607.3
35°	1326.2
37.5°	1042.7
40°	781.4
42.5°	569.4
45°	414.2
47.5°	295.8
50°	199.6
52.5°	125.8
55°	74.0
57.5°	37.0
60°	17.3
62.5°	14.8
65°	12.4
67.5°	9.9
70°	7.4
72.5°	4.9
75°	4.9
77.5°	2.5
80°	2.5
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)