

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580482

Luminaire Tested: **HC435D010-HM43040927-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580482  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC435D010-HM43040927-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2654.2 lumens  
Efficiency: N/A  
Efficacy: 78.8 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580482

CATALOG NUMBER: HC435D010-HM43040927-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580482

CATALOG NUMBER: HC435D010-HM43040927-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	230545
5°	229098
10°	224232
15°	219268
20°	209139
25°	193584
30°	168378
35°	127162
40°	92150
45°	72008
50°	61578
55°	53267
60°	49067
65°	44917
70°	41942
75°	38459
80°	36013
85°	34532



TEST NUMBER: P580482

CATALOG NUMBER: HC435D010-HM43040927-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.8	6.6
10°-20°	481.0	18.1
20°-30°	646.8	24.4
30°-40°	531.8	20.0
40°-50°	326.6	12.3
50°-60°	226.0	8.5
60°-70°	154.1	5.8
70°-80°	85.9	3.2
80°-90°	27.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1302.5	49.1
0°-40°	1834.3	69.1
0°-60°	2386.9	89.9
0°-90°	2654.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2654.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1869	
5°	1850	175
15°	1717	481
25°	1422	647
35°	844	532
45°	413	327
55°	248	226
65°	154	154
75°	81	86
85°	24	27
90°	0	



TEST NUMBER: P580482

CATALOG NUMBER: HC435D010-HM43040927-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1869.1
2.5°	1855.9
5°	1850.3
7.5°	1829.6
10°	1790.3
12.5°	1754.7
15°	1717.1
17.5°	1662.6
20°	1593.3
22.5°	1510.7
25°	1422.4
27.5°	1315.5
30°	1182.2
32.5°	1019.0
35°	844.5
37.5°	694.3
40°	572.3
42.5°	478.5
45°	412.8
47.5°	362.2
50°	320.9
52.5°	283.4
55°	247.7
57.5°	221.4
60°	198.9
62.5°	176.4
65°	153.9
67.5°	135.1
70°	116.3
72.5°	97.6
75°	80.7
77.5°	63.8
80°	50.7
82.5°	37.5
85°	24.4
87.5°	13.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)