

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580507

Luminaire Tested: **HC435D010-HM43040935-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580507  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC435D010-HM43040935-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2725.3 lumens  
Efficiency: N/A  
Efficacy: 80.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580507

CATALOG NUMBER: HC435D010-HM43040935-41WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P580507

CATALOG NUMBER: HC435D010-HM43040935-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	271792
5°	272050
10°	272566
15°	276553
20°	269651
25°	253004
30°	223782
35°	170167
40°	107221
45°	61559
50°	32660
55°	13569
60°	3626
65°	3065
70°	2272
75°	2002
80°	1492
85°	2972



TEST NUMBER: P580507

CATALOG NUMBER: HC435D010-HM43040935-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.0	7.7
10°-20°	606.4	22.3
20°-30°	846.3	31.1
30°-40°	696.4	25.6
40°-50°	286.9	10.5
50°-60°	64.7	2.4
60°-70°	10.4	0.4
70°-80°	3.9	0.1
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1661.7	61.0
0°-40°	2358.1	86.5
0°-60°	2709.7	99.4
0°-90°	2725.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2725.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2204	
5°	2197	209
15°	2166	606
25°	1859	846
35°	1130	696
45°	353	287
55°	63	65
65°	10	10
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P580507

CATALOG NUMBER: HC435D010-HM43040935-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2203.5
2.5°	2193.0
5°	2197.2
7.5°	2188.8
10°	2176.2
12.5°	2169.9
15°	2165.7
17.5°	2128.0
20°	2054.3
22.5°	1961.9
25°	1859.0
27.5°	1735.1
30°	1571.2
32.5°	1369.6
35°	1130.1
37.5°	888.5
40°	665.9
42.5°	485.2
45°	352.9
47.5°	252.1
50°	170.2
52.5°	107.1
55°	63.1
57.5°	31.5
60°	14.7
62.5°	12.6
65°	10.5
67.5°	8.4
70°	6.3
72.5°	4.2
75°	4.2
77.5°	2.1
80°	2.1
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)