

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592540

Luminaire Tested: **HC405D010-HM40525850-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC405D010-HM40525850-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 633.8 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592540

CATALOG NUMBER: HC405D010-HM40525850-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P592540

CATALOG NUMBER: HC405D010-HM40525850-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55678
5°	55259
10°	53819
15°	52407
20°	50063
25°	46640
30°	41062
35°	32389
40°	23508
45°	17287
50°	14046
55°	11785
60°	10657
65°	9807
70°	9124
75°	8340
80°	7529
85°	6652



TEST NUMBER: P592540

CATALOG NUMBER: HC405D010-HM40525850-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.1	6.6
10°-20°	115.1	18.2
20°-30°	156.0	24.6
30°-40°	133.9	21.1
40°-50°	79.1	12.5
50°-60°	50.1	7.9
60°-70°	33.6	5.3
70°-80°	18.6	2.9
80°-90°	5.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	313.2	49.4
0°-40°	447.1	70.6
0°-60°	576.3	90.9
0°-90°	633.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	633.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	451	
5°	446	42
15°	410	115
25°	343	156
35°	215	134
45°	99	79
55°	55	50
65°	34	34
75°	18	19
85°	5	5
90°	0	



TEST NUMBER: P592540

CATALOG NUMBER: HC405D010-HM40525850-41NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	451.4
2.5°	448.2
5°	446.3
7.5°	440.4
10°	429.7
12.5°	420.5
15°	410.4
17.5°	397.5
20°	381.4
22.5°	363.4
25°	342.7
27.5°	318.3
30°	288.3
32.5°	252.9
35°	215.1
37.5°	178.8
40°	146.0
42.5°	118.8
45°	99.1
47.5°	84.8
50°	73.2
52.5°	63.6
55°	54.8
57.5°	47.9
60°	43.2
62.5°	38.7
65°	33.6
67.5°	29.5
70°	25.3
72.5°	21.2
75°	17.5
77.5°	13.8
80°	10.6
82.5°	7.4
85°	4.7
87.5°	1.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)