

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581051

Luminaire Tested: **HC405D010-HM40525927-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581051  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC405D010-HM40525927-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 545.4 lumens  
Efficiency: N/A  
Efficacy: 90.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581051

CATALOG NUMBER: HC405D010-HM40525927-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581051

CATALOG NUMBER: HC405D010-HM40525927-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	45860
5°	46208
10°	46780
15°	47963
20°	48317
25°	46926
30°	43027
35°	35401
40°	25811
45°	16746
50°	9460
55°	4494
60°	1776
65°	1080
70°	721
75°	477
80°	213
85°	425



TEST NUMBER: P581051

CATALOG NUMBER: HC405D010-HM40525927-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.6	6.5
10°-20°	105.9	19.4
20°-30°	157.0	28.8
30°-40°	145.0	26.6
40°-50°	75.7	13.9
50°-60°	20.8	3.8
60°-70°	4.0	0.7
70°-80°	1.1	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.6	54.7
0°-40°	443.6	81.3
0°-60°	540.1	99.0
0°-90°	545.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	545.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	372	
5°	373	36
15°	376	106
25°	345	157
35°	235	145
45°	96	76
55°	21	21
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581051

CATALOG NUMBER: HC405D010-HM40525927-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	371.8
2.5°	370.8
5°	373.2
7.5°	374.2
10°	373.5
12.5°	374.2
15°	375.6
17.5°	374.2
20°	368.1
22.5°	358.1
25°	344.8
27.5°	326.7
30°	302.1
32.5°	271.0
35°	235.1
37.5°	197.5
40°	160.3
42.5°	126.1
45°	96.0
47.5°	70.4
50°	49.3
52.5°	32.8
55°	20.9
57.5°	12.3
60°	7.2
62.5°	5.1
65°	3.7
67.5°	2.7
70°	2.0
72.5°	1.4
75°	1.0
77.5°	0.7
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)