

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592790

Luminaire Tested: **HC435D010-HM43040950-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592790  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC435D010-HM43040950-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3563.3 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592790

CATALOG NUMBER: HC435D010-HM43040950-41WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P592790

CATALOG NUMBER: HC435D010-HM43040950-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55	55	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	287864
5°	292071
10°	301235
15°	321885
20°	341083
25°	337330
30°	302772
35°	235638
40°	159648
45°	99656
50°	43137
55°	14451
60°	3626
65°	2452
70°	1515
75°	1001
80°	1492
85°	0



TEST NUMBER: P592790

CATALOG NUMBER: HC435D010-HM43040950-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	226.6	6.4
10°-20°	715.6	20.1
20°-30°	1121.2	31.5
30°-40°	967.6	27.2
40°-50°	445.0	12.5
50°-60°	75.6	2.1
60°-70°	8.5	0.2
70°-80°	3.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2063.3	57.9
0°-40°	3030.9	85.1
0°-60°	3551.5	99.7
0°-90°	3563.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3563.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2334	
5°	2359	227
15°	2521	716
25°	2479	1121
35°	1565	968
45°	571	445
55°	67	76
65°	8	9
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P592790

CATALOG NUMBER: HC435D010-HM43040950-41WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2333.8
2.5°	2333.8
5°	2358.9
7.5°	2382.1
10°	2405.1
12.5°	2453.5
15°	2520.7
17.5°	2577.4
20°	2598.5
22.5°	2566.9
25°	2478.6
27.5°	2335.9
30°	2125.8
32.5°	1861.1
35°	1564.9
37.5°	1266.6
40°	991.5
42.5°	758.4
45°	571.3
47.5°	401.2
50°	224.8
52.5°	124.0
55°	67.2
57.5°	33.6
60°	14.7
62.5°	10.5
65°	8.4
67.5°	6.3
70°	4.2
72.5°	4.2
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)