

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581068

Luminaire Tested: **HC405D010-HM40525930-41NDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581068  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC405D010-HM40525930-41NDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 527.4 lumens  
Efficiency: N/A  
Efficacy: 87.9 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581068

CATALOG NUMBER: HC405D010-HM40525930-41NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581068

CATALOG NUMBER: HC405D010-HM40525930-41NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63	63	63	63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58	58	58	58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	68420
5°	67158
10°	63714
15°	59571
20°	54093
25°	47865
30°	39823
35°	28715
40°	17921
45°	10327
50°	5834
55°	2774
60°	1603
65°	1226
70°	829
75°	524
80°	568
85°	425



TEST NUMBER: P581068

CATALOG NUMBER: HC405D010-HM40525930-41NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.7	9.6
10°-20°	130.1	24.7
20°-30°	160.0	30.3
30°-40°	118.9	22.5
40°-50°	48.3	9.2
50°-60°	13.4	2.5
60°-70°	4.2	0.8
70°-80°	1.4	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.9	64.6
0°-40°	459.7	87.2
0°-60°	521.4	98.9
0°-90°	527.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	527.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	555	
5°	542	51
15°	466	130
25°	352	160
35°	191	119
45°	59	48
55°	13	13
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581068

CATALOG NUMBER: HC405D010-HM40525930-41NDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	554.7
2.5°	549.3
5°	542.4
7.5°	528.8
10°	508.7
12.5°	487.7
15°	466.5
17.5°	441.1
20°	412.1
22.5°	382.9
25°	351.7
27.5°	317.9
30°	279.6
32.5°	235.9
35°	190.7
37.5°	148.1
40°	111.3
42.5°	81.3
45°	59.2
47.5°	42.6
50°	30.4
52.5°	20.9
55°	12.9
57.5°	8.4
60°	6.5
62.5°	5.3
65°	4.2
67.5°	3.1
70°	2.3
72.5°	1.9
75°	1.1
77.5°	0.8
80°	0.8
82.5°	0.3
85°	0.3
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)