

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580568

Luminaire Tested: **HC440D010-HM43040830-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040830-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4023.1 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580568

CATALOG NUMBER: HC440D010-HM43040830-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P580568

CATALOG NUMBER: HC440D010-HM43040830-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	592540
5°	591782
10°	580251
15°	539544
20°	464023
25°	372756
30°	291036
35°	203761
40°	104564
45°	53099
50°	26596
55°	9935
60°	4021
65°	3181
70°	1947
75°	1287
80°	1918
85°	0



TEST NUMBER: P580568

CATALOG NUMBER: HC440D010-HM43040830-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	451.9	11.2
10°-20°	1166.3	29.0
20°-30°	1256.5	31.2
30°-40°	825.5	20.5
40°-50°	256.7	6.4
50°-60°	50.4	1.3
60°-70°	10.7	0.3
70°-80°	3.9	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2874.7	71.5
0°-40°	3700.2	92.0
0°-60°	4007.3	99.6
0°-90°	4023.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4023.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4804	
5°	4780	452
15°	4225	1166
25°	2739	1256
35°	1353	826
45°	304	257
55°	46	50
65°	11	11
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P580568

CATALOG NUMBER: HC440D010-HM43040830-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4803.9
2.5°	4779.5
5°	4779.5
7.5°	4741.5
10°	4632.8
12.5°	4458.9
15°	4225.2
17.5°	3912.7
20°	3535.1
22.5°	3127.5
25°	2738.9
27.5°	2377.5
30°	2043.4
32.5°	1728.1
35°	1353.2
37.5°	942.9
40°	649.4
42.5°	448.3
45°	304.4
47.5°	206.5
50°	138.6
52.5°	87.0
55°	46.2
57.5°	19.1
60°	16.3
62.5°	13.6
65°	10.9
67.5°	8.2
70°	5.4
72.5°	5.4
75°	2.7
77.5°	2.7
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)