

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592551

Luminaire Tested: **HC405D010-HM40525950-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC405D010-HM40525950-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 575.7 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592551

CATALOG NUMBER: HC405D010-HM40525950-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P592551

CATALOG NUMBER: HC405D010-HM40525950-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63	63	63	63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58	58	58	58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74673
5°	73312
10°	69525
15°	65023
20°	59055
25°	52261
30°	43469
35°	31350
40°	19547
45°	11286
50°	6352
55°	3032
60°	1727
65°	1313
70°	902
75°	572
80°	568
85°	708



TEST NUMBER: P592551

CATALOG NUMBER: HC405D010-HM40525950-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.3	9.6
10°-20°	142.0	24.7
20°-30°	174.7	30.3
30°-40°	129.7	22.5
40°-50°	52.7	9.2
50°-60°	14.6	2.5
60°-70°	4.5	0.8
70°-80°	1.5	0.3
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.1	64.6
0°-40°	501.8	87.2
0°-60°	569.2	98.9
0°-90°	575.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	575.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	605	
5°	592	55
15°	509	142
25°	384	175
35°	208	130
45°	65	53
55°	14	15
65°	4	5
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P592551

CATALOG NUMBER: HC405D010-HM40525950-41NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	605.4
2.5°	599.5
5°	592.1
7.5°	577.1
10°	555.1
12.5°	532.4
15°	509.2
17.5°	481.4
20°	449.9
22.5°	417.9
25°	384.0
27.5°	347.1
30°	305.2
32.5°	257.5
35°	208.2
37.5°	161.7
40°	121.4
42.5°	88.8
45°	64.7
47.5°	46.4
50°	33.1
52.5°	22.8
55°	14.1
57.5°	9.1
60°	7.0
62.5°	5.8
65°	4.5
67.5°	3.3
70°	2.5
72.5°	2.0
75°	1.2
77.5°	0.8
80°	0.8
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)