

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580586

Luminaire Tested: **HC440D010-HM43040835-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040835-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4034.6 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580586

CATALOG NUMBER: HC440D010-HM43040835-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P580586

CATALOG NUMBER: HC440D010-HM43040835-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	594242
5°	593479
10°	581904
15°	541090
20°	465349
25°	373831
30°	291862
35°	204333
40°	104870
45°	53238
50°	26673
55°	9957
60°	4046
65°	3181
70°	1984
75°	1287
80°	1918
85°	0



TEST NUMBER: P580586

CATALOG NUMBER: HC440D010-HM43040835-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	453.2	11.2
10°-20°	1169.6	29.0
20°-30°	1260.1	31.2
30°-40°	827.9	20.5
40°-50°	257.4	6.4
50°-60°	50.5	1.3
60°-70°	10.8	0.3
70°-80°	4.0	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2882.9	71.5
0°-40°	3710.8	92.0
0°-60°	4018.7	99.6
0°-90°	4034.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4034.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4818	
5°	4793	453
15°	4237	1170
25°	2747	1260
35°	1357	828
45°	305	257
55°	46	51
65°	11	11
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P580586

CATALOG NUMBER: HC440D010-HM43040835-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4817.7
2.5°	4793.2
5°	4793.2
7.5°	4755.1
10°	4646.0
12.5°	4471.7
15°	4237.3
17.5°	3923.9
20°	3545.2
22.5°	3136.4
25°	2746.8
27.5°	2384.4
30°	2049.2
32.5°	1733.1
35°	1357.0
37.5°	945.6
40°	651.3
42.5°	449.6
45°	305.2
47.5°	207.0
50°	139.0
52.5°	87.2
55°	46.3
57.5°	19.1
60°	16.4
62.5°	13.7
65°	10.9
67.5°	8.2
70°	5.5
72.5°	5.5
75°	2.7
77.5°	2.7
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)