

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581121

Luminaire Tested: **HC455D010-HM44560827-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC455D010-HM44560827-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4340.1 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581121

CATALOG NUMBER: HC455D010-HM44560827-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P581121

CATALOG NUMBER: HC455D010-HM44560827-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	561876
5°	550130
10°	519881
15°	485567
20°	444084
25°	396573
30°	333023
35°	234283
40°	144512
45°	86521
50°	50986
55°	25397
60°	13099
65°	8610
70°	5301
75°	4241
80°	2060
85°	4104



TEST NUMBER: P581121

CATALOG NUMBER: HC455D010-HM44560827-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.9	9.6
10°-20°	1062.9	24.5
20°-30°	1325.5	30.5
30°-40°	976.4	22.5
40°-50°	401.6	9.3
50°-60°	117.3	2.7
60°-70°	30.2	0.7
70°-80°	9.3	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2803.4	64.6
0°-40°	3779.8	87.1
0°-60°	4298.7	99.0
0°-90°	4340.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4340.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4555	
5°	4443	415
15°	3802	1063
25°	2914	1326
35°	1556	976
45°	496	402
55°	118	117
65°	30	30
75°	9	9
85°	3	2
90°	0	



TEST NUMBER: P581121

CATALOG NUMBER: HC455D010-HM44560827-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4555.3
2.5°	4508.1
5°	4443.1
7.5°	4325.1
10°	4150.8
12.5°	3979.6
15°	3802.5
17.5°	3604.7
20°	3383.2
22.5°	3153.0
25°	2913.9
27.5°	2648.1
30°	2338.2
32.5°	1963.2
35°	1555.9
37.5°	1195.6
40°	897.5
42.5°	664.2
45°	496.0
47.5°	366.1
50°	265.7
52.5°	183.0
55°	118.1
57.5°	70.9
60°	53.1
62.5°	38.4
65°	29.5
67.5°	20.7
70°	14.7
72.5°	11.8
75°	8.9
77.5°	5.9
80°	2.9
82.5°	2.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)