

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592802

Luminaire Tested: **HC440D010-HM43040850-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040850-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4192.7 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592802

CATALOG NUMBER: HC440D010-HM43040850-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P592802

CATALOG NUMBER: HC440D010-HM43040850-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62				62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58				58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54				54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51				51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	542782
5°	531446
10°	502221
15°	469069
20°	429003
25°	383085
30°	321700
35°	226302
40°	139601
45°	83573
50°	49259
55°	24537
60°	12655
65°	8318
70°	5121
75°	4051
80°	1989
85°	3963



TEST NUMBER: P592802

CATALOG NUMBER: HC440D010-HM43040850-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.8	9.6
10°-20°	1026.8	24.5
20°-30°	1280.5	30.5
30°-40°	943.2	22.5
40°-50°	387.9	9.3
50°-60°	113.3	2.7
60°-70°	29.1	0.7
70°-80°	9.0	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2708.1	64.6
0°-40°	3651.4	87.1
0°-60°	4152.7	99.0
0°-90°	4192.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4192.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4400	
5°	4292	401
15°	3673	1027
25°	2815	1281
35°	1503	943
45°	479	388
55°	114	113
65°	28	29
75°	8	9
85°	3	2
90°	0	



TEST NUMBER: P592802

CATALOG NUMBER: HC440D010-HM43040850-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4400.5
2.5°	4354.9
5°	4292.2
7.5°	4178.1
10°	4009.8
12.5°	3844.4
15°	3673.3
17.5°	3482.2
20°	3268.3
22.5°	3045.9
25°	2814.8
27.5°	2558.2
30°	2258.7
32.5°	1896.5
35°	1502.9
37.5°	1155.1
40°	867.0
42.5°	641.7
45°	479.1
47.5°	353.7
50°	256.7
52.5°	176.8
55°	114.1
57.5°	68.5
60°	51.3
62.5°	37.1
65°	28.5
67.5°	20.0
70°	14.2
72.5°	11.4
75°	8.5
77.5°	5.7
80°	2.8
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)