

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581128

Luminaire Tested: **HC455D010-HM44560827-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC455D010-HM44560827-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4263.4 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581128

CATALOG NUMBER: HC455D010-HM44560827-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581128

CATALOG NUMBER: HC455D010-HM44560827-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361452
5°	359539
10°	352963
15°	345522
20°	330753
25°	307552
30°	272221
35°	214844
40°	160759
45°	123676
50°	100340
55°	83223
60°	73588
65°	68091
70°	62859
75°	57760
80°	52422
85°	41891



TEST NUMBER: P581128

CATALOG NUMBER: HC455D010-HM44560827-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.5	6.4
10°-20°	758.8	17.8
20°-30°	1030.4	24.2
30°-40°	892.5	20.9
40°-50°	560.4	13.1
50°-60°	352.5	8.3
60°-70°	231.5	5.4
70°-80°	127.8	3.0
80°-90°	35.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2063.7	48.4
0°-40°	2956.3	69.3
0°-60°	3869.2	90.8
0°-90°	4263.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4263.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2930	
5°	2904	275
15°	2706	759
25°	2260	1030
35°	1427	893
45°	709	560
55°	387	353
65°	233	232
75°	121	128
85°	30	35
90°	0	



TEST NUMBER: P581128

CATALOG NUMBER: HC455D010-HM44560827-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2930.4
2.5°	2912.6
5°	2903.8
7.5°	2874.3
10°	2818.1
12.5°	2762.0
15°	2705.8
17.5°	2629.1
20°	2519.8
22.5°	2395.7
25°	2259.8
27.5°	2103.3
30°	1911.3
32.5°	1677.9
35°	1426.8
37.5°	1196.4
40°	998.4
42.5°	842.0
45°	709.0
47.5°	608.5
50°	522.9
52.5°	449.0
55°	387.0
57.5°	333.8
60°	298.3
62.5°	265.8
65°	233.3
67.5°	200.9
70°	174.3
72.5°	144.8
75°	121.2
77.5°	94.5
80°	73.8
82.5°	50.2
85°	29.6
87.5°	11.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)