

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592808

Luminaire Tested: **HC440D010-HM43040850-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040850-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4840.1 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592808

CATALOG NUMBER: HC440D010-HM43040850-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P592808

CATALOG NUMBER: HC440D010-HM43040850-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391006
5°	396746
10°	409187
15°	437234
20°	463301
25°	458224
30°	411273
35°	320097
40°	216857
45°	135381
50°	58565
55°	19612
60°	4934
65°	3327
70°	2056
75°	1334
80°	1989
85°	0



TEST NUMBER: P592808

CATALOG NUMBER: HC440D010-HM43040850-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.8	6.4
10°-20°	972.0	20.1
20°-30°	1522.9	31.5
30°-40°	1314.4	27.2
40°-50°	604.4	12.5
50°-60°	102.6	2.1
60°-70°	11.6	0.2
70°-80°	4.1	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2802.7	57.9
0°-40°	4117.0	85.1
0°-60°	4824.1	99.7
0°-90°	4840.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4840.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3170	
5°	3204	308
15°	3424	972
25°	3367	1523
35°	2126	1314
45°	776	604
55°	91	103
65°	11	12
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P592808

CATALOG NUMBER: HC440D010-HM43040850-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3170.0
2.5°	3170.0
5°	3204.3
7.5°	3235.7
10°	3267.0
12.5°	3332.6
15°	3424.0
17.5°	3501.0
20°	3529.6
22.5°	3486.8
25°	3366.9
27.5°	3172.9
30°	2887.6
32.5°	2528.0
35°	2125.8
37.5°	1720.5
40°	1346.8
42.5°	1030.1
45°	776.1
47.5°	545.0
50°	305.2
52.5°	168.4
55°	91.2
57.5°	45.6
60°	20.0
62.5°	14.2
65°	11.4
67.5°	8.5
70°	5.7
72.5°	5.7
75°	2.8
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)