

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581137

Luminaire Tested: **HC455D010-HM44560830-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581137  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC455D010-HM44560830-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4252.3 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581137

CATALOG NUMBER: HC455D010-HM44560830-41WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P581137

CATALOG NUMBER: HC455D010-HM44560830-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	424075
5°	424469
10°	425281
15°	431487
20°	420746
25°	394762
30°	349175
35°	265513
40°	167280
45°	96045
50°	50947
55°	21139
60°	5674
65°	4787
70°	3534
75°	3098
80°	2344
85°	4670



TEST NUMBER: P581137

CATALOG NUMBER: HC455D010-HM44560830-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	326.0	7.7
10°-20°	946.2	22.3
20°-30°	1320.5	31.1
30°-40°	1086.6	25.6
40°-50°	447.6	10.5
50°-60°	100.9	2.4
60°-70°	16.2	0.4
70°-80°	6.0	0.1
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2592.7	61.0
0°-40°	3679.3	86.5
0°-60°	4227.8	99.4
0°-90°	4252.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4252.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3438	
5°	3428	326
15°	3379	946
25°	2901	1320
35°	1763	1087
45°	551	448
55°	98	101
65°	16	16
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P581137

CATALOG NUMBER: HC455D010-HM44560830-41WDBB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3438.1
2.5°	3421.7
5°	3428.2
7.5°	3415.2
10°	3395.5
12.5°	3385.7
15°	3379.0
17.5°	3320.1
20°	3205.4
22.5°	3061.1
25°	2900.6
27.5°	2707.2
30°	2451.6
32.5°	2136.9
35°	1763.3
37.5°	1386.3
40°	1038.9
42.5°	757.1
45°	550.6
47.5°	393.3
50°	265.5
52.5°	167.2
55°	98.3
57.5°	49.2
60°	23.0
62.5°	19.7
65°	16.4
67.5°	13.2
70°	9.8
72.5°	6.5
75°	6.5
77.5°	3.3
80°	3.3
82.5°	3.3
85°	3.3
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)