

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581141

Luminaire Tested: **HC455D010-HM44560830-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC455D010-HM44560830-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5235.8 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581141

CATALOG NUMBER: HC455D010-HM44560830-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581141

CATALOG NUMBER: HC455D010-HM44560830-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	440221
5°	443524
10°	449066
15°	460360
20°	463721
25°	450453
30°	413011
35°	339838
40°	247707
45°	160779
50°	90650
55°	43031
60°	16997
65°	10536
70°	7105
75°	4670
80°	2344
85°	4670



TEST NUMBER: P581141

CATALOG NUMBER: HC455D010-HM44560830-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.0	6.5
10°-20°	1016.3	19.4
20°-30°	1507.5	28.8
30°-40°	1392.3	26.6
40°-50°	727.0	13.9
50°-60°	199.3	3.8
60°-70°	38.4	0.7
70°-80°	10.8	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2865.8	54.7
0°-40°	4258.2	81.3
0°-60°	5184.4	99.0
0°-90°	5235.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5235.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3569	
5°	3582	342
15°	3605	1016
25°	3310	1507
35°	2257	1392
45°	922	727
55°	200	199
65°	36	38
75°	10	11
85°	3	2
90°	0	



TEST NUMBER: P581141

CATALOG NUMBER: HC455D010-HM44560830-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3569.0
2.5°	3559.0
5°	3582.1
7.5°	3591.9
10°	3585.4
12.5°	3591.9
15°	3605.1
17.5°	3591.9
20°	3532.8
22.5°	3437.8
25°	3309.8
27.5°	3135.9
30°	2899.8
32.5°	2601.2
35°	2256.9
37.5°	1896.0
40°	1538.4
42.5°	1210.4
45°	921.7
47.5°	675.8
50°	472.4
52.5°	314.9
55°	200.1
57.5°	118.1
60°	68.9
62.5°	49.2
65°	36.1
67.5°	26.2
70°	19.7
72.5°	13.2
75°	9.8
77.5°	6.5
80°	3.3
82.5°	3.3
85°	3.3
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)