

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580642

Luminaire Tested: **HC440D010-HM43040930-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040930-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3364.7 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580642

CATALOG NUMBER: HC440D010-HM43040930-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580642

CATALOG NUMBER: HC440D010-HM43040930-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285261
5°	283763
10°	278565
15°	272696
20°	261040
25°	242729
30°	214837
35°	169550
40°	126881
45°	97598
50°	79175
55°	65675
60°	58096
65°	53761
70°	49588
75°	45560
80°	41412
85°	32975



TEST NUMBER: P580642

CATALOG NUMBER: HC440D010-HM43040930-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.7	6.4
10°-20°	598.9	17.8
20°-30°	813.2	24.2
30°-40°	704.4	20.9
40°-50°	442.2	13.1
50°-60°	278.2	8.3
60°-70°	182.8	5.4
70°-80°	100.8	3.0
80°-90°	27.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1628.7	48.4
0°-40°	2333.1	69.3
0°-60°	3053.5	90.8
0°-90°	3364.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3364.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2313	
5°	2292	217
15°	2136	599
25°	1784	813
35°	1126	704
45°	560	442
55°	305	278
65°	184	183
75°	96	101
85°	23	28
90°	0	



TEST NUMBER: P580642

CATALOG NUMBER: HC440D010-HM43040930-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2312.7
2.5°	2298.7
5°	2291.8
7.5°	2268.5
10°	2224.1
12.5°	2179.8
15°	2135.5
17.5°	2074.9
20°	1988.7
22.5°	1890.7
25°	1783.5
27.5°	1660.0
30°	1508.4
32.5°	1324.2
35°	1126.0
37.5°	944.2
40°	788.0
42.5°	664.4
45°	559.5
47.5°	480.2
50°	412.6
52.5°	354.3
55°	305.4
57.5°	263.4
60°	235.5
62.5°	209.9
65°	184.2
67.5°	158.5
70°	137.5
72.5°	114.2
75°	95.6
77.5°	74.7
80°	58.3
82.5°	39.7
85°	23.3
87.5°	9.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)