

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580644

Luminaire Tested: **HC440D010-HM43040930-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC440D010-HM43040930-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3294.9 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580644

CATALOG NUMBER: HC440D010-HM43040930-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580644

CATALOG NUMBER: HC440D010-HM43040930-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	286187
5°	284395
10°	278352
15°	272198
20°	259609
25°	240320
30°	209026
35°	157835
40°	114402
45°	89399
50°	76450
55°	66127
60°	60933
65°	55745
70°	52076
75°	47752
80°	44679
85°	42882



TEST NUMBER: P580644

CATALOG NUMBER: HC440D010-HM43040930-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.9	6.6
10°-20°	597.1	18.1
20°-30°	802.9	24.4
30°-40°	660.2	20.0
40°-50°	405.4	12.3
50°-60°	280.6	8.5
60°-70°	191.2	5.8
70°-80°	106.6	3.2
80°-90°	33.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1616.9	49.1
0°-40°	2277.0	69.1
0°-60°	2963.1	89.9
0°-90°	3294.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3294.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2320	
5°	2297	217
15°	2132	597
25°	1766	803
35°	1048	660
45°	512	405
55°	308	281
65°	191	191
75°	100	107
85°	30	34
90°	0	



TEST NUMBER: P580644

CATALOG NUMBER: HC440D010-HM43040930-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2320.2
2.5°	2303.9
5°	2296.9
7.5°	2271.3
10°	2222.4
12.5°	2178.1
15°	2131.6
17.5°	2064.0
20°	1977.8
22.5°	1875.3
25°	1765.8
27.5°	1633.0
30°	1467.6
32.5°	1264.9
35°	1048.2
37.5°	861.9
40°	710.5
42.5°	594.0
45°	512.5
47.5°	449.6
50°	398.4
52.5°	351.8
55°	307.5
57.5°	274.9
60°	247.0
62.5°	218.9
65°	191.0
67.5°	167.7
70°	144.4
72.5°	121.2
75°	100.2
77.5°	79.3
80°	62.9
82.5°	46.6
85°	30.3
87.5°	16.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)