

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592913

Luminaire Tested: **HC4R55D010-HM44560850-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P592913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R55D010-HM44560850-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5827.8 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592913

CATALOG NUMBER: HC4R55D010-HM44560850-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P592913

CATALOG NUMBER: HC4R55D010-HM44560850-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80		
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74		
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69		
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60		
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56		
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52		
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	660429
5°	674591
10°	701216
15°	701490
20°	648564
25°	560460
30°	455952
35°	334944
40°	193606
45°	90446
50°	41813
55°	14537
60°	4638
65°	3269
70°	2705
75°	1763
80°	0
85°	0



TEST NUMBER: P592913

CATALOG NUMBER: HC4R55D010-HM44560850-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	525.6	9.0
10°-20°	1522.4	26.1
20°-30°	1874.9	32.2
30°-40°	1368.8	23.5
40°-50°	446.1	7.7
50°-60°	74.5	1.3
60°-70°	11.6	0.2
70°-80°	3.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3922.9	67.3
0°-40°	5291.7	90.8
0°-60°	5812.4	99.7
0°-90°	5827.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5827.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5354	
5°	5448	526
15°	5493	1522
25°	4118	1875
35°	2224	1369
45°	518	446
55°	68	75
65°	11	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P592913

CATALOG NUMBER: HC4R55D010-HM44560850-42RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5354.3
2.5°	5358.0
5°	5448.3
7.5°	5553.4
10°	5598.6
12.5°	5583.5
15°	5493.4
17.5°	5267.9
20°	4941.0
22.5°	4546.5
25°	4118.1
27.5°	3671.0
30°	3201.3
32.5°	2720.4
35°	2224.4
37.5°	1724.6
40°	1202.4
42.5°	785.2
45°	518.5
47.5°	341.9
50°	217.9
52.5°	127.8
55°	67.6
57.5°	26.3
60°	18.8
62.5°	15.1
65°	11.2
67.5°	7.5
70°	7.5
72.5°	3.7
75°	3.7
77.5°	3.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)