

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581270

Luminaire Tested: **HC460D010-HM44560827-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560827-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4546.1 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581270

CATALOG NUMBER: HC460D010-HM44560827-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P581270

CATALOG NUMBER: HC460D010-HM44560827-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	669606
5°	668747
10°	655713
15°	609714
20°	524364
25°	421233
30°	328865
35°	230248
40°	118170
45°	59989
50°	30050
55°	11225
60°	4539
65°	3590
70°	2200
75°	1430
80°	2131
85°	0



TEST NUMBER: P581270

CATALOG NUMBER: HC460D010-HM44560827-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	510.7	11.2
10°-20°	1318.0	29.0
20°-30°	1419.9	31.2
30°-40°	932.9	20.5
40°-50°	290.1	6.4
50°-60°	56.9	1.3
60°-70°	12.1	0.3
70°-80°	4.4	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3248.5	71.5
0°-40°	4181.4	92.0
0°-60°	4528.4	99.6
0°-90°	4546.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4546.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5429	
5°	5401	511
15°	4775	1318
25°	3095	1420
35°	1529	933
45°	344	290
55°	52	57
65°	12	12
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P581270

CATALOG NUMBER: HC460D010-HM44560827-41NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5428.7
2.5°	5401.1
5°	5401.1
7.5°	5358.1
10°	5235.3
12.5°	5038.8
15°	4774.7
17.5°	4421.6
20°	3994.8
22.5°	3534.2
25°	3095.1
27.5°	2686.8
30°	2309.0
32.5°	1952.9
35°	1529.1
37.5°	1065.5
40°	733.9
42.5°	506.7
45°	343.9
47.5°	233.4
50°	156.6
52.5°	98.2
55°	52.2
57.5°	21.5
60°	18.4
62.5°	15.3
65°	12.3
67.5°	9.2
70°	6.1
72.5°	6.1
75°	3.0
77.5°	3.0
80°	3.0
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)